



# Hostalen ACP 5831 D

**Polyethylene, High Density**

## Product Description

Hostalen ACP 5831 D is a high density polyethylene (HDPE) resin used in small blow molding applications such as thin-wall packaging, consumer goods and toys. It exhibits a very good combination of high stiffness and high stress cracking resistance. Hostalen ACP 5831 D is delivered in pellet form, demonstrates good organoleptic properties, contains antioxidants and has a broad molecular weight distribution. Hostalen ACP 5831 D is not intended for use in medical and pharmaceutical applications.

## Product Characteristics

<b>Status</b>	Commercial: Active
<b>Test Method used</b>	ISO
<b>Availability</b>	Europe, Asia-Pacific, Australia/NZ, Africa-Middle East, Latin America
<b>Processing Methods</b>	Extrusion Blow Molding
<b>Features</b>	Antioxidant, High ESCR (Environmental Stress Cracking Resistance), High Rigidity
<b>Typical Customer Applications</b>	Blow Moulding Applications, Bottles and vials, Bottles For Consumer Goods, Consumer Packaging, Jerry Cans, Sports, Leisure and Toys

Typical Properties	Method	Value	Unit
<b>Physical</b>			
Density	ISO 1183	0.958	g/cm <sup>3</sup>
Melt flow rate (MFR)	ISO 1133		
(190°C/2.16kg)		0.30	g/10 min
(190°C/21.6kg)		22	g/10 min
(190°C/5.0kg)		1.2	g/10 min
Bulk density	ISO 60	>0.500	g/cm <sup>3</sup>
FNCT (3.5 MPa, 2% Igepal BC/9, 80°C)	ISO 16770	8	h
<b>Mechanical</b>			
ESCR	ASTM D 1693	150	h
<i>Note: Method B; Tested in 10% nonionic surfactants</i>			
Tensile Modulus	ISO 527-1, -2	1350	MPa
Tensile Stress at Yield	ISO 527-1, -2	28.0	MPa
Tensile Strain at Yield	ISO 527-1, -2	7.5	%
Tensile Impact Strength	ISO 8256	75.0	kJ/m <sup>2</sup>

*Note:* notched, -30°C

**Impact**

Charpy notched impact strength (-30 °C, Type 1, Notch A) ISO 179 6.5 kJ/m<sup>2</sup>

**Hardness**

Shore hardness (Shore D)	ISO 868	64	
Ball indentation hardness (H 132/30)	ISO 2039-1	60	MPa

## Additional Properties

Recommended processing temperature 180°C - 210°C

**Notes**

Typical properties; not to be construed as specifications.

## Further Information

### *Hostalen ACP 5831 D*

**Conveying:** Conveying equipment should be designed to prevent production and accumulation of fines and dust particles that are contained in polymer resins. These particles can under certain conditions pose an explosion hazard. We recommend the conveying system used is equipped with adequate filters, is operated and maintained that no leak develops and adequate grounding exists at all times.

**Health and Safety:**

The resin is manufactured to the highest standards but, special requirements apply to certain applications such as food end-use contact and direct medical use. For specific information on regulatory compliance contact your local representative.

Workers should be protected from the possibility of skin or eye contact with molten polymer. Safety glasses are suggested as a minimal precaution to prevent mechanical or thermal injury to the eyes.

Molten polymer may be degraded if it is exposed to air during any of the processing and off-line operations. The products of degradation have an unpleasant odour. In higher concentrations they may cause irritation of the mucus membranes. Fabrication areas should be ventilated to carry away fumes or vapours. Legislation on the control of emissions and pollution prevention must be observed. If the principles of sound manufacturing practice are adhered to and the place of work is well ventilated, no health hazards are involved in processing the resin.

The resin will burn when supplied with excess heat and oxygen. It should be handled and stored away from contact with direct flames and/or ignition sources. In burning the resin

contributes high heat and may generate a dense black smoke. Starting fires can be extinguished by water, developed fires should be extinguished by heavy foams forming an aqueous or polymeric film. For further information about safety in handling and processing please refer to the Material Safety Data Sheet.

**Storage:**

The resin is packed in 25 kg bags or in bulk containers protecting it from contamination. If it is stored under adverse conditions, i. e. if there are large fluctuations in ambient temperature and the atmospheric humidity is high, moisture may condense inside the packaging. Under these circumstances, it is recommended to dry the resin before use. Unfavourable storage conditions may also intensify the resin's slight characteristic odour.

The resin is subjected to degradation by ultra-violet radiations or by high storage temperatures. Therefore the resin must be protected from direct sunlight, temperatures above 40°C and high atmospheric humidity during storage. The resin can be stored over a period of more than 6 month without significant changes in the specified properties, appropriate storage conditions provided. Higher storage temperatures reduce the storage time.

The information submitted is based on our current knowledge and experience. In view of the many factors that may affect processing and application, these data do not relieve processors of the responsibility of carrying out their own tests and experiments; neither do they imply any legally binding assurance of certain properties or of suitability for a specific purpose. The data do not relieve the customer from his obligation to control the resin upon arrival and to complain about faults. It is the responsibility of those to whom we supply our products to ensure that any proprietary rights and existing laws and legislation are observed.

© LyondellBasell Industries Holdings, B.V. 2014

LyondellBasell markets this product through the following entities:

- Equistar Chemicals, LP
- Basell Sales & Marketing Company B.V.
- Basell Asia Pacific Limited
- Basell International Trading FZE
- LyondellBasell Australia Pty Ltd

For the contact details of the LyondellBasell company selling this product in your country, please visit <http://www.lyb.com/>.

Before using a product sold by a company of the LyondellBasell family of companies, users should make their own independent determination that the product is suitable for the intended use and can be used safely and legally.

**SELLER MAKES NO WARRANTY; EXPRESS OR IMPLIED (INCLUDING ANY WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR ANY WARRANTY) OTHER THAN AS SEPARATELY AGREED TO BY THE PARTIES IN A CONTRACT.**

This product(s) may not be used in:

(i) any U.S. FDA Class I, Health Canada Class I, and/or European Union Class I Medical Devices, without prior notification to Seller for each specific product and application; or

(ii) the manufacture of any of the following, without prior written approval by Seller for each specific product and application: (1) U.S. FDA Class II, Health Canada Class II or Class III, and/or European Union Class II Medical Devices; (2) film, overwrap and/or product packaging that is considered a part or component of one of the aforementioned Medical Devices; (3) packaging in direct contact with a pharmaceutical active ingredient and/or dosage form that is intended for inhalation, injection, intravenous, nasal, ophthalmic (eye), digestive, or topical (skin) administration; (4) tobacco related products and applications; (5) electronic cigarettes and similar devices; and (6) pressure pipe or fittings that are considered a part or component of a nuclear reactor.

(iii) Additionally, the product(s) may not be used in: (1) U.S. FDA Class III, Health Canada Class IV, and/or European Class III Medical Devices; (2) applications involving permanent implantation into the body; (3) life-sustaining medical applications; and (4) lead, asbestos or MTBE related applications.

All references to U.S. FDA, Health Canada, and European Union regulations include another country's equivalent regulatory classification.

Users should review the applicable Material Safety Data Sheet before handling the product.

*Addhere, Adflex, Adstif, Adsyl, Akoafloor, Akoalit, Alastian, Alathon, Alkylate, Amazing Chemistry, Aquamarine, Aquathene, Arctic Plus, Arctic Shield, Avant, Catalloy, Clyrell, CRP, Crystex, Dexflex, Duopac, Duoprime, Explore & Experiment, Filmex, Flexathene, Fueling the power to win, Get in touch with, Glacido, Hifax, Histif, Hostacom, Hostalen PP, Hostalen ACP, Ideal, Indure, Integrate, Koattro, LIPP, Lucalen, Luflexen, Lupolen, Lupolex, Luposim, Lupostress, Lupotech, Metocene, Microthene, Moplen, MPDIOL, Nerolex, Nexprene, Petrothene, Plexar, Polymeg, Pristene, Prodflex, Pro-fax, Punctilious, Purell, Refax, SAA100, SAA101, Sequel, Softell, Spherilene, Spheripol, Spherizone, Starflex, Stretchene, Superflex, TBAC, Tebol, T-Hydro, Toppyl, Trans4m, Tufflo, Ultrathene, Vacido and Valtec,* are trademarks owned and/or used by the LyondellBasell family of companies.

*Adsyl, Akoafloor, Akoalit, Alastian, Alathon, Aquamarine, Arctic Plus, Arctic Shield, Avant, CRP, Crystex, Dexflex, Duopac, Duoprime, Explore & Experiment, Filmex, Flexathene, Hifax, Hostacom, Hostalen, Ideal, Integrate, Koattro, Lucalen, Lupolen, Metocene, Microthene, Moplen, MPDIOL, Nexprene, Petrothene, Plexar, Polymeg, Pristene, Pro-fax, Punctilious, Purell, Sequel, Softell, Spheripol, Spherizone, Starflex, Tebol, T-Hydro, Toppyl, Tufflo, Ultrathene* are registered in the U.S. Patent and Trademark Office.

Release Date: 18 Feb 2013